



Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering Guide

Example: CB100 A K5812

Product Code	CB100	Composite
Finish	A H	Black Bronze
Wattage	K5812	(2) 18W 1141 (120/12)

Specifications

HOUSING:

Die-cast aluminum back box contains less than 0.3% copper to prevent corrosion in concrete or masonry applications. Horizontal Louver Faceplate is an injection molded RYTON® composite with frosted tempered glass and stainless steel screws.

FINISH:

Zinc-rich primer and thermoset powdercoat for durability. Composite is textured, pressure formed, molded-in-color.

OPTICAL ASSEMBLY:

Horizontal Louver Faceplate - Injection molded RYTON® composite with frosted tempered glass, with stainless steel screws.

LAMPING:

Two 18W maximum S-8 (1141) lamps (Single contact bayonet base).

ELECTRICAL ASSEMBLY:

Single contact bayonet (S-8). 12 volt fixture is pre-wired with 6-ft. pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards. ADA Compliant when used in indoor and outdoor wall applications.

Height :	Width:	Depth:	Max. Weight:
3 1/2" (90mm)	9" (229mm)	4 11/16" (103mm)	3.5 lb.

