


| | |
|-----------|------|
| Project: | |
| Location: | |
| Cat.No: | |
| Type: | |
| Lamps: | Qty: |
| Notes: | |

Ordering Information

Catalog Number


SAB
Side Angle Bracket



| Cat. # | Finish | Tenon Size | Wt lbs |
|--------|------------|------------|--------|
| SAB-P | Primer | 2-3/8" | 8 |
| SAB-DB | Dk. Bronze | 2-3/8" | 8 |
| SAB-G | Galvanized | 2-3/8" | 8 |

Catalog Number

WSRAB-2
Right Angle Bracket for Wall Mounting




Removable Cap

| Cat. # | Finish | Tenon Size | Wt lbs |
|-----------|------------|------------|--------|
| WSRAB-2P | Primer | 2-3/8" | 10 |
| WSRAB-2DB | Dk. Bronze | 2-3/8" | 10 |
| WSRAB-2G | Galvanized | 2-3/8" | 10 |

Catalog Number


WRAB
Right Angle Bracket for Wall Mounting



| Cat. # | Finish | Wt lbs |
|---------|------------|--------|
| WRAB-P | Primer | 8 |
| WRAB-DB | Dk. Bronze | 8 |
| WRAB-G | Galvanized | 8 |

Catalog Number


WRABH
Right Angle Bracket for Wall Mounting



| Cat. # | Finish | Tenon Size | A | Wt lbs |
|-------------|------------|------------|---------|--------|
| WRABH-P | Primer | 2-3/8" | 8-1/2" | 10 |
| WRABH-14-P | Primer | 2-3/8" | 14-1/2" | 12 |
| WRABH-DB | Dk. Bronze | 2-3/8" | 8-1/2" | 10 |
| WRABH-14-DB | Dk. Bronze | 2-3/8" | 14-1/2" | 12 |
| WRABH-G | Galvanized | 2-3/8" | 8-1/2" | 10 |
| WRABH-14-G | Galvanized | 2-3/8" | 14-1/2" | 12 |

Catalog Number


WDRAB-2
Wall Double Right Angle Bracket



| Cat. # | Finish | Tenon Size | Wt lbs |
|-----------|------------|------------|--------|
| WDRAB-2P | Primer | 2-3/8" | 22 |
| WDRAB-2DB | Dk. Bronze | 2-3/8" | 22 |
| WDRAB-2G | Galvanized | 2-3/8" | 22 |

Catalog Number

WVT-2
Wall Vertical Tenon Bracket



| Cat. # | Finish | Tenon Size | Wt lbs |
|---------|------------|------------|--------|
| WVT-2P | Primer | 2-3/8" | 5 |
| WVT-2DB | Dk. Bronze | 2-3/8" | 5 |
| WVT-2G | Galvanized | 2-3/8" | 5 |

Side, Tenon & Reducer Brackets PA-46032

Ordering Information

Catalog Number

PB-2
Parapet Bracket

| Cat. # | Finish | Tenon Size | Wt lbs |
|--------|------------|------------|--------|
| PB-2P | Primer | 2-3/8" | 4 |
| PB-2DB | Dk. Bronze | 2-3/8" | 4 |
| PB-2G | Galvanized | 2-3/8" | 4 |

Catalog Number

SPTA-4DB
Square Pole Tenon Adaptor

| Cat. # | Finish | Tenon Size | A | Wt lbs |
|----------|------------|------------|----|--------|
| SPTA-4DB | Dk. Bronze | 2-3/8" | 3" | 7 |
| SPTA-5DB | Dk. Bronze | 2-3/8" | 4" | 8 |

Catalog Number

STB-2
Side Tenon Pole Bracket

| Cat. # | Finish | Tenon Size | Wt lbs |
|---------|------------|------------|--------|
| STB-2P | Primer | 2-3/8" | 5 |
| STB-2DB | Dk. Bronze | 2-3/8" | 5 |
| STB-2G | Galvanized | 2-3/8" | 5 |

Catalog Number

SPRAB
Right Angle Bracket for Square Steel Pole Mounting

| Cat. # | Finish | Tenon Size | A | Wt lbs |
|-----------|------------|------------|--------|--------|
| SPRAB-4P | Primer | 2-3/8" | 3-3/4" | 8 |
| SPRAB-5P | Primer | 2-3/8" | 4-3/4" | 8 |
| SPRAB-6P | Primer | 2-3/8" | 5-3/4" | 9 |
| SPRAB-4DB | Dk. Bronze | 2-3/8" | 3-3/4" | 8 |
| SPRAB-5DB | Dk. Bronze | 2-3/8" | 4-3/4" | 8 |
| SPRAB-6DB | Dk. Bronze | 2-3/8" | 5-3/4" | 9 |
| SPRAB-4G | Galvanized | 2-3/8" | 3-3/4" | 8 |
| SPRAB-5G | Galvanized | 2-3/8" | 4-3/4" | 8 |
| SPRAB-6G | Galvanized | 2-3/8" | 5-3/4" | 9 |


Catalog Number

SPRABH
Right Angle Bracket for Square Steel Pole Mounting


| Cat. # | Finish | Tenon Size | A | B | Wt lbs |
|---------------|------------|------------|---------|--------|--------|
| SPRABH-4P | Primer | 2-3/8" | 8-1/2" | 3-3/4" | 10 |
| SPRABH-5P | Primer | 2-3/8" | 8-1/2" | 4-3/4" | 10 |
| SPRABH-6P | Primer | 2-3/8" | 8-1/2" | 5-3/4" | 11 |
| SPRABH-14-4P | Primer | 2-3/8" | 14-1/2" | 3-3/4" | 12 |
| SPRABH-14-5P | Primer | 2-3/8" | 14-1/2" | 4-3/4" | 12 |
| SPRABH-14-6P | Primer | 2-3/8" | 14-1/2" | 5-3/4" | 13 |
| SPRABH-4DB | Dk. Bronze | 2-3/8" | 8-1/2" | 3-3/4" | 10 |
| SPRABH-5DB | Dk. Bronze | 2-3/8" | 8-1/2" | 4-3/4" | 10 |
| SPRABH-6DB | Dk. Bronze | 2-3/8" | 8-1/2" | 5-3/4" | 11 |
| SPRABH-14-4DB | Dk. Bronze | 2-3/8" | 14-1/2" | 3-3/4" | 12 |
| SPRABH-14-5DB | Dk. Bronze | 2-3/8" | 14-1/2" | 4-3/4" | 12 |
| SPRABH-14-6DB | Dk. Bronze | 2-3/8" | 14-1/2" | 5-3/4" | 13 |
| SPRABH-4G | Galvanized | 2-3/8" | 8-1/2" | 3-3/4" | 10 |
| SPRABH-5G | Galvanized | 2-3/8" | 8-1/2" | 4-3/4" | 10 |
| SPRABH-6G | Galvanized | 2-3/8" | 8-1/2" | 5-3/4" | 11 |
| SPRABH-14-4G | Galvanized | 2-3/8" | 14-1/2" | 3-3/4" | 12 |
| SPRABH-14-5G | Galvanized | 2-3/8" | 14-1/2" | 4-3/4" | 12 |
| SPRABH-14-6G | Galvanized | 2-3/8" | 14-1/2" | 5-3/4" | 13 |

Side, Tenon & Reducer Brackets PA-46032

Ordering Information



| Cat. # | Finish | Tenon Size | A | Wt lbs |
|-------------|------------|------------|----------|--------|
| RPTR-30-2P | Primer | 2-3/8" | 3-1/4" | 8 |
| RPTR-35-2P | Primer | 2-3/8" | 3-13/16" | 10 |
| RPTR-40-2P | Primer | 2-3/8" | 4-1/4" | 11 |
| RPTR-30-2DB | Dk. Bronze | 2-3/8" | 3-1/4" | 8 |
| RPTR-35-2DB | Dk. Bronze | 2-3/8" | 3-13/16" | 10 |
| RPTR-40-2DB | Dk. Bronze | 2-3/8" | 4-1/4" | 11 |
| RPTR-30-2G | Galvanized | 2-3/8" | 3-1/4" | 8 |
| RPTR-35-2G | Galvanized | 2-3/8" | 3-13/16" | 10 |
| RPTR-40-2G | Galvanized | 2-3/8" | 4-1/4" | 11 |



| Cat. # | Finish | Tenon Size | A | B | Wt lbs |
|-----------|------------|------------|----------|---------|--------|
| WPTT-45P | Primer | 2-3/8" | 4-15/16" | 5-9/16" | 7 |
| WPTT-65P | Primer | 2-3/8" | 6-7/16" | 5-9/16" | 8 |
| WPTT-76P | Primer | 2-3/8" | 7-3/16" | 6-7/16" | 9 |
| WPTT-77P | Primer | 2-3/8" | 7-3/16" | 7-3/16" | 10 |
| WPTT-45DB | Dk. Bronze | 2-3/8" | 4-15/16" | 5-9/16" | 7 |
| WPTT-65DB | Dk. Bronze | 2-3/8" | 6-7/16" | 5-9/16" | 8 |
| WPTT-76DB | Dk. Bronze | 2-3/8" | 7-3/16" | 6-7/16" | 9 |
| WPTT-77DB | Dk. Bronze | 2-3/8" | 7-3/16" | 7-3/16" | 10 |
| WPTT-45G | Galvanized | 2-3/8" | 4-15/16" | 5-9/16" | 7 |
| WPTT-65G | Galvanized | 2-3/8" | 6-7/16" | 5-9/16" | 8 |
| WPTT-76G | Galvanized | 2-3/8" | 7-3/16" | 6-7/16" | 9 |
| WPTT-77G | Galvanized | 2-3/8" | 7-3/16" | 7-3/16" | 10 |

