



## Ordering guide

Example: HFP620 P3 A N PM

Product Code	Post Diameter	Finish	Arm Accessory	Post Matching
<b>HFP620</b>			<b>N</b>	<b>PM</b>
<b>HFP620</b> Twin	<b>P3</b> 3" Post Mount <b>P4</b> 4" Post Mount <b>P5</b> 5" Post Mount	<b>A</b> Black <b>B</b> White <b>G</b> Verde <b>H</b> Bronze <b>I</b> Gray <b>J</b> Green	<b>N</b> None	<b>PM</b> Post Matching

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

## Specifications

### Housing

6063-T6 Extruded aluminum.

### Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

### Warranty

Three-year limited warranty.

Height	Length	EPA
50 1/2" (128 cm)	58" (147 cm)	2.05 sq. ft.

