

by (Signify

Urban

### Grande Essex


7610 Side arm mount

Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	



Example: 7610 ABS A D 50H E B B

Product Code	7610	Grande Essex
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VCP VCP VCP VCP VCP VCP VCP VCP VCP	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Panel/Globe	A B C D E M P Q	Clear Acrylic Opal Acrylic Clear Seeded Acrylic Bronze Tone Acrylic Clear Textured Acrylic Opal Polycarbonate Clear Polycarbonate Prismatic Polycarbonate
Socket	D G L R	Medium Mogul LED Induction
Wattage/Source	50H 70H 100H 150H 50S 70S 100S 150S 150I 55R 85R LED	50W MH 70W MH 150W MH 50W HPS 70W HPS 100W HPS 150W HPS 150W INC. 55W Induction 85W Induction LED
Voltage	E F G H	120V 208V 240V 277V



## 7610 Grande Essex

Side arm mount

#### **Ordering Guide**

Example: 7610 ABS A D 50H E B B

	1 -	AU = 1/
Distribution	В	6" Type V
		Distrib.
	С	6" Type III
		Distrib.
	D	8" Type V
		Distrib.
	E	8" Type II
		Distrib.
	N	None
Photoeye	В	Button Eye *1
-	Ν	None

\*1 Button Eye (B) only available in 120V (E).

#### Specifications

#### CONSTRUCTION:

Cast aluminum turned top. Cast aluminum roof cap. Cast aluminum hinged square roof. Cast aluminum square cage with frog bottom. Brass anodized aluminum sleeve. Cast aluminum bracket arm and ballast housing with wall plate.

#### FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

#### PANELS/LENS/GLOBE:

See lenses for available options.

#### LAMPING:

Lamp is not included.

#### **ELECTRICAL ASSEMBLY:**

Lantern will be prewired and tested. All electrical components are ETL listed.

#### BALLAST:

Ballast mounted inside moisture proof housing. (Customer must specify wattage and voltage.)

#### MOUNTING:

See template for dimensions & mounting instructions.

#### WARRANTY:

Three-year limited warranty.

#### **CERTIFICATIONS:**

ETL Listed to U.S. safety standards for wet locations. cETL Listed to Canadian safety standards for wet locations.

#### Height:

35 1/2"

#### Width: 16"

Projection: 25 1/8"

## Top to Outlet: 26 1/2"

Max. Weight: 44 lbs.

# Signify

© 2019 Signify Holding. All rights reserved. This document may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporatic 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008