

Project: _____

Location: _____

Cat.No: _____


Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering Guide

Example: 5534 ABS A D 50H E B B



Product Code	5534	Manor
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Panel/Globe	A B C D E M P Q	Clear Acrylic Opal Acrylic Clear Seeded Acrylic Bronze Tone Acrylic Clear Textured Acrylic Opal Polycarbonate Clear Polycarbonate Prismatic Polycarbonate
Socket	D G L	Medium Mogul LED
Wattage/Source	50H 70H 100H 150H 35S 50S 70S 100S 150S 150I 55R 85R LED	50W MH 70W MH 100W MH 150W MH 35W HPS 50W HPS 70W HPS 100W HPS 150W HPS 150W INC. 55W Induction 85W Induction LED

5534 Manor

Post top

Ordering Guide

Example: 5534 ABS A D 50H E B B

Voltage	E	120V
	F	208V
	G	240V
	H	277V
Distribution	B	6" Type V Distrib.
	C	6" Type III Distrib.
	N	None
	V	Type V - Cone
Photoeye	B	Button Eye *1
	N	None

*1 Button Eye (B) only available in 120V (E).

Specifications

CONSTRUCTION:

Cast aluminum finial and cap. Cast aluminum hex roof secures to cage with thumbscrews. Cast aluminum hex cage. Cast aluminum post fitter slips over 3" dia. post or tenon.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

PANELS/LENS/GLOBE:

See lenses for available options.

LAMPING:

Lamp is not included.

ELECTRICAL ASSEMBLY:

Lantern will be prewired and tested. All electrical components are ETL listed.

BALLAST:

Ballast and component parts mounted inside 2-piece cast aluminum moisture proof ballast compartment. (Customer must specify voltage and wattage.)

MOUNTING:

Fixture mounts to 3" dia. post or tenon.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL Listed to Canadian safety standards for wet locations.

Height:

31 3/4"

Width:

14"

Fitter:

3" I.D.

EPA:

1.30

Max. Weight:

23 lbs.

