



Ordering guide

Example: HFP1410 P4 B F PM

Product Code	Post Diameter	Finish	Arm Accessory	Post Matching
HFP1410				PM
HFP1410 Single	P4 4" Post Mount P5 5" Post Mount P6 6" Post Mount	B White G Verde H Bronze J Green A Black	N None F Finial R Twistlock receptacle	PM Post Matching

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Specifications

Housing

6063-T6 Extruded aluminum.

Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. Polymer has molded-in color and texture for color fastness and durability. For larger projects where a custom color is required, contact the factory for more information.

Certifications

Manufactured to ISO 9001:2008 Standards.

Warranty

Three-year limited warranty.

EPA

2.50 sq. ft.

Height	Length	Overall Length
66" (168cm)	66" (168cm)	74" (188cm)

