

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____



Ordering Guide

Example: 233-4FL ABS

Product Code	233-4FL	Stop Sign Frame with Post Fitter
Finish	ABS	Antique Brass
	ACP	Antique Copper
	ARD	Antique Red
	ASI	Antique Silver
	BLK	Black
	BRN	Brown
	BRZ	Bronze
	FGN	Forest Green
	GRA	Granite
	IRN	Ironstone
	RBZ	Rustic Bronze
	SRT	Shadow Rust
	VBZ	Verde Bronze
	VCP	Verde Copper
	VGN	Verde
	VTC	Vintage Copper
	WBZ	Weathered Bronze
	WHT	White

Specifications

CONSTRUCTION:

Two piece cast and fabricated aluminum assembly for 30" (across flats) octagonal stop sign. (Stop sign not supplied by Hanover Lantern.) Sign frame secures to rear support with (4) 1/4-20 screws, nuts and washers. (2) 1/4-20 screws, nuts and washers supplied to attach stop sign to sign frame. Cast aluminum 4" I.D. fluted post fitter. (4) 5/16-18 set screws and (2) 1/4-20 threaded rods with lock washers and nuts secure sign frame to fitter. (6) 5/16-18 stainless steel set screws secure fitter to 4" dia. fluted post. (Post must be ordered separately.)

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

WARRANTY:

Three-year limited warranty.

Height:

43 1/8"

Width:

31 1/2"

