


Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____



Ordering Guide

Example: P9500 10 A T D

Product Code	P9500	
Pole Height	10	10'
	12	12'
	14	14'
	16	16'
Finish	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green
Outlet Location (Optional)	T	12" Down from Top - Aligned with House Side
Outlet Options (Optional)	D	Standard Duplex
	G	GFI Duplex

Specifications

HOUSING:

356-T6 Sand Cast Aluminum. 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel . Tenon is 356 HM sand cast aluminum.

FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:

Three-year limited warranty.

OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

P9500 P9500

Pole

Specifications

Tenon/Top:

3" OD

Bolt Circle:

8" - 9"

Anchor Rods:

(4) 3/4" dia. x 19"

Base Dimensions:

9" sq.

Hand Hole :

2" x 4" Oval

Shaft:

5" Straight/Flat Fluted

Wall Thickness:

0.188 - 0.267 Aluminum

Height :

10', 12', 14', 16'

Pole EPA Values

	Height			
Windspeed(mph)	10'	12'	14'	16'
80	24.8700	20.4700	13.6800	11.4400
100	15.7100	12.8500	8.5100	7.0300

