

# Stonco

by @ignify

Wall Mount

Wall pack

WP30/WP50/WP75



## Proven design meets LED technology

With efficacies up to 118 LPW, the Stonco LED wall packs help you to upgrade from costly HID fixtures with confidence.



The Wall pack family features energy-saving LED technology, two different sizes & wattage choices of 30, 50 and 75W. The 50 watt Wall pack provides the same illumination as a 100W HID, and uses over 50% less energy. The glass refractor lens design cuts down on glare, and the housing is one-piece die-cast aluminum for strength and durability.

**Move into the future with time-proven design from a name you can trust.**




# WP Wall pack





## Proven design combines with the latest technology

- An easy switch from costly HID fixtures.
- Flexible options – choose from 30, 50 and 75 watts in two different sizes.
- The 50 watt Wall pack provides the equivalent illumination to 100W HID, and uses over 50% less energy.\*
- Glass refractor lens design cuts down on glare.
- One-piece die-cast aluminum housing.
- 5 year limited warranty.


\*Based on comparison between 100W HPS Wall pack at 115W providing 6100 lumens and 50W WP LED providing 5500 lumens.



WP30



WP50 & WP75



### Ordering guide

Example: WP-50-NW-G1--8-BZ

Luminaire	Wattage	Generation	Options	Voltage	Finish
<b>WP</b>		<b>NW-G1</b>		<b>8</b>	<b>BZ</b>
<b>WP</b> Traditional Wall Pack	<b>30</b> 30W <b>50</b> 50W <b>75</b> 75W	<b>NW-G1</b> Neutral White, 4000K, 70CRI, Generation 1	-- None <b>PCB</b> Button Photocell	<b>8</b> 120-277 Volts	<b>BZ</b> Bronze

### Performance data

Catalog Code	Lumens
WP-30-NW-G1-8-BZ	3355
WP-50-NW-G1-8-BZ	5541
WP-75-NW-G1-8-BZ	8999

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

