

Project: \_\_\_\_\_


Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_



### Ordering Guide

Example: P150 8 A T D

Product Code	P150	
Pole Height	8	8'
	10	10'
Finish	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green
Outlet Location (Optional)	T	12" Down from Top - Aligned with House Side
Outlet Options (Optional)	D	Standard Duplex
	G	GFI Duplex

### Specifications

#### OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

#### HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy . 319 Permanent mold aluminum . 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel .

#### FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

# P150 P150

## Pole

### Specifications

---

**WARRANTY:**

Three-year limited warranty.

**Tenon/Top:**

3" OD

**Bolt Circle:**

7"

**Anchor Rods:**

(3) 1/2" dia. x 15 1/2"

**Base Dimensions:**

9 5/8" dia. x 1 3/8"

**Base Cover:**

(Included) 10 1/4" dia. x 2 3/4"

**Hand Hole :**

2" x 4" Oval

**Shaft:**

3" Straight

**Wall Thickness:**

0.125 Aluminum

**Height :**

8', 10'

### Pole EPA Values

---

Windspeed(mph)	Height	
	8'	10'
80	3.1900	2.1900
100	1.8000	1.0700

