

# Stonco

by  Signify

Wall Mount

Tall wall pack

TW20



## Tall, brilliant & and full of life...

The Stonco LED Tall wall pack is an easy choice for almost any outdoor lighting location with durable illumination that was built to last.

This lightweight and compact wall pack is only 20 watts, but equal to 70 watts of HID illumination, so you can count on serious energy savings. Installation is quick and easy, the Tall wall pack mounts to a standard 3 and a half or 4 inch j- box. The bronze housing is die cast aluminum and impact resistant polycarbonate, with a frosted lens. Combine that strength with a long LED lifetime and this wall mounted fixture is one you can count on.

**Choose the Tall wall pack for your next project.**



# TW LED Tall wall pack




- Lightweight, compact and built to last.
- Provides up to 83% energy savings over 70W Metal Halide luminaires.\*
- The bronze housing is die cast aluminum and impact resistant polycarbonate, with a frosted lens.
- Installation is quick and easy, by mounting to a standard 3 1/2 or 4" junction box.
- Rated for temperatures from -40° to 40°.
- Lifetime >100,000 hours.\*\*
- 5 year limited warranty.


\* Based on comparison between TW20 @ 20W and 70W Metal halide.

\*\*Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology.

Front view



Side view



## Ordering guide

Example: TW-20-NW-G1-8-BZ

Luminaire	Wattage	Generation	Photocell	Voltage	Finish
<b>TW</b>	<b>20</b>	<b>NW-G1</b>			<b>BZ</b>
TW Tall Wall Pack LED	20 20W	NW-G1 Neutral White, 4000K, 70CRI, Generation 1	-- No Photocell PCB Button Photocell <sup>1</sup>	8 120-277 Volts 1 120 Volts	BZ Bronze

1. Only available in 120V.

## Performance data

Catalog Code	Lumens
TW-20-NW-G1-8-BZ	2277

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

