



Lumec features a range of steel poles suited for multiple outdoor applications, all designed and manufactured for superior quality.



	Good	Good	Good	Good	Better	Better	Better	Better	Best	Best	Best	Best
	SPR4	SPR5	SPS4	SPS5	SM6	SM8	SSM8	RS61	RS804	RS805	RS856	R90
Pole Style	Round Straight	Round Straight	Square Straight	Square Straight	Round Straight	Round Straight	Round Straight	Round Straight	Round Straight	Round Straight	Round Straight	16-Flute Round Tapered
Base Style	Optional Base Covers	Optional Base Covers	Square Base Cover	Square Base Cover	Bottleneck	Bottleneck	Bottleneck	Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck	Fluted Bottleneck
Height	8', 10', 12', 14', 15', 16', 18', 20'	14', 15', 16', 18', 20', 22', 25', 30'	8', 10', 12', 14', 15', 16', 18', 20'	15', 18', 20', 25', 30'	8', 10', 12', 14', 15', 16', 18', 20'	8', 10', 12', 14', 15', 16', 18', 20'	18', 20', 22', 24', 26', 28'	8', 10', 12', 14', 15', 16', 18', 20'	8', 10', 12', 14', 15', 16', 18', 20'	14', 15', 16', 18', 20', 22', 25', 30'	8', 10', 12', 14', 16', 18', 20', 22'	10', 12', 14', 15', 16', 18', 20'
Diameter	4"	5"	4"	5"	4"	4"	5-9/16"	4"	4"	5"	5-9/16"	6-5/8"
Thickness	0.120", 0.188", 0.250"	0.150", 0.188", 0.250"	0.120", 0.188", 0.250"	0.120", 0.188", 0.250"	0.120", 0.188", 0.250"	0.120", 0.188", 0.250"	0.250"	0.120", 0.188", 0.250"	0.120", 0.188", 0.250"	0.150", 0.188", 0.250"	0.250"	0.120"
Base	10" Square	12-1/2" Square	10" Square	12-1/2" Square	16" Round	18" Round	18" Round	18" Round	16-1/2" Round	16-1/2" Round	16-1/2" Round	17-1/2" Round
Bolt Circle	8-1/2"	12-1/2"	8-1/2"	12-1/2"	10-1/2"	12-1/2"	12-1/2"	12-1/2"	8-1/2"	12-1/2"	12-1/2"	12-1/2"
Optional Bases	LBC1, LBC2, LBC3, LBC4C	LBC1, B105, B50	-	-	-	-	-	-	-	-	-	-
EPA @ 90 MPH	6.43-28.85	11.41-30.00	15.10-30.00	18.85-30.00	8.64-30.00	9.10-30.00	25.36-30.00	5.32-30.00	6.43-28.85	11.41-30.00	11.44-30.00	30.00
EPA @ 110 MPH	3.50-19.40	7.25-30.00	9.65-30.00	12.47-30.00	5.14-30.00	5.49-30.00	17.19-30.00	2.94-20.59	3.50-19.40	7.25-30.00	7.39-30.00	25.20-30.00
EPA @ 120 MPH	2.56-16.27	5.96-25.56	7.90-30.00	10.38-30.00	4.03-30.00	4.32-30.00	14.44-30.00	2.21-17.35	2.56-16.27	5.96-30.00	6.08-30.00	21.14-30.00
EPA @ 150 MPH	1.36-10.44	3.48-16.47	4.56-30.00	6.47-30.00	2.37-20.32	2.56-22.17	9.13-21.20	1.22-11.20	1.36-10.44	3.48-30.00	3.60-25.12	13.66-22.40
Options	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Hinged Base, Banner Arm, Plant Support, Mid-Pole Luminaire, Optional Base Covers	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Shorting Cap, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire	Buried Pole, Loudspeaker Outlet, Photoelectric Cell, Duplex Receptacle, GFI, Banner Arm, Plant Support, Mid-Pole Luminaire
Finish	Refer to Finishes below											
Link												


Available in Textured and Smooth finishes



Available in a variety of standard colors and finishes to suit your needs

These colors are available in smooth finishes (to order remove TX from code). Due to the porous nature of castings, a smooth finish may present minor imperfections. Textured finishes conceal pores and provide a more uniform finish.

Textured only Smooth only



Special colors

SCL Special Color (liquid)
SCP Special Color (powder)

It is now possible to order smaller quantities of powder paint for a premium. Your representative can advise you if a powder coat paint can be developed for your project.

Custom colors

We support custom color options to the ultimate in color matching opportunities with your site lighting needs.