LUMEC

by (s) ignify

Tunnel

TunnelView

TULS/TULM/TULL



Tunnels demand reliable solutions with maximum durability

With TunnelView, savings add up quickly due to fast, simple installation, partnered with significantly less and easier servicing than traditional products, which helps minimize costly traffic disruptions.







TULS/TULM/TULL TunnelView

Tunnel and underpass luminaire

Stainless steel screws -Heat sink -All exposed screws are stainless Built into the housing, ensures high efficacy and superior steel with ceramic primer seal for cooling by natural convection air flow pattern, always close high resistance to corrosion to LEDs and driver optimizing their efficiency and life Glass lens -Offers IK09 LEDs + Lens impact protection High performance optics optimized for maximum spacing, target lumens, and lighting uniformity Optional Tool-less Metal core board latches -Ensures greater heat transfer and longer lifespan For easy access Service Tag -Signify's innovative way to provide assistance throughout the life of the product Durable construction -Secured door -Gasketing -Rugged, anodized low copper Door is removable and secured IP66 rated luminaire die-cast aluminum housing for maximum with tether to prevent accidental dropping or disengagement durability in harsh environments

Additional features -

- Three sizes for application flexibility
- Lumen output ranges from 1,700 to 53,900
- · Efficacy up to 144 LPW
- Nine optical distributions for maximum versatility
- Color temperatures in 2700K, 3000K, or 4000K
- Swivel, slipfitter, or seven fixed mounting brackets available
- Controls options: 0-10V Dimming, DALI, Sensor Ready, NYX Hemera ready
- Finish available in black, bronze, or gray
- Junction box option for through wire and continuous row mounting

SR Driver & Sensor Receptacle -

Optional to add flexibility for now or in the future, luminaires ship with a protective cap





Signify

© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.