

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: 201-EBX V ABS A B WHT 12

Product Code	201-EBX	Street Sign
Lettering	V	Vinyl
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Print	A B N	Single Sided Double Sided None
Vinyl Lettering Style	B	Block *1
Letter Color	WHT	White
Wording	12	Spaces (12)

*1 Vinyl Lettering Style Only

Specifications

CONSTRUCTION:

Extruded aluminum 30" x 9" sign with engineer grade reflective green vinyl both sides. attached to cast aluminum post fitter. Cast aluminum cross arm bracket. (Sign has 29" x 7" lettering area on both sides.)

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

MOUNTING:

To mount 201-EBX top sign assembly, Customer must order 201-EB3 bottom sign and fitter assembly.

WARRANTY:

Three-year limited warranty.

201-EBX Accessories

Street sign

Specifications

Height:

10 3/8"

Width:

30"

