

CHLORIDE

by  Signify

Exit/Emergency

SCL series

LED die-formed steel exit/unit
combo, NYC Approved 8" letters



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Example: SCLRW3

SCLRW3 Combo – Red LED, white housing, universal white exit face, 3-12 Watt tungsten lamp heads

Accessories

WG5 – Wire Guard

Note :

For black housing change the "W" to a "B" in above catalog number .

codes and standards

- UL listed to Standard 924
- NFPA 101 (Life Safety Code)
- NFPA 70 (National Electric Code)
- New York City Approved (8" letters)
- UL listed for damp location

construction

- Housing and canopy constructed of 20 gauge steel .
- Field selectable chevrons .
- Housing is finished in a white durable powder coat .
- Black housing available .

installation

- Wall mount hardware is included .
- Combos come provided with an extra lamp head for 3 lamp head applications . (3rd lamp head to be field installed .

electronics

- Isolated short circuit and voltage protection circuit .
- Test switch and LED indicator light .
- Low voltage disconnect feature prevents deep battery discharge .
- 24 hour recharge after 90 minute discharge .
- 120/277 VAC , Dual Voltage input .
- Power Consumption: 14 . 3W max .

LED/lamps

- Exit face illumination is provided by a special high intensity indirect red LED strip .
- Letter brightness and illumination uniformity exceed UL requirements .
- Uniform 8" letter illumination (1" stroke) .
- Lamp heads are high impact flame retardant plastic .
- Combo lamp heads contain 12 watt tungsten lamps .
- Two or three lamp heads are mounted on top of combo .

battery

- Maintenance free 6V sealed lead acid battery .
- Provides a minimum 90 minutes of emergency illumination while in the emergency mode .

warranty

- Five year warranty on exit . (lamps not included .)



SCL LED die-formed steel exit/unit combo

NYC Approved 8" letters

dimensions

