

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: HFP710 P3 A F PM

Product Code	HFP710	Single
Post diameter	P3 P4 P5 P6	3" Post Mount 4" Post Mount 5" Post Mount 6" Post Mount
Finish	A B G H I J	Black White Verde Bronze Gray Green
Arm Accessory	F R N	Finial Twistlock Receptacle None
Post Machining	PM	Post Machining

Specifications

HOUSING:

6063-T6 Extruded aluminum .

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:

Three-year limited warranty.

Height :

35 1/4" (90 cm)

Length:

49 3/4" (126 cm)

EPA:

3.00 sq. ft.

