



Ordering guide

Example: PTH2570 P3 A

Product Code	Post Diameter	Finish
PTH2570		
PTH2570 Triple	P3 3" Post Mount P4 4" Post Mount	A Black B White G Verde H Bronze J Green

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Specifications

Housing

356 HM high-strength, low-copper, proprietary cast aluminum alloy.

Finish


Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

Mounting

Cast Aluminum Hub mounts to a 3" OD x 3" long (P3) [if applicable] or 4" OD x 6 1/2" long (P4) [if applicable] tenon and is secured with at least (3) 5/16"-18 stainless steel set screws.

Warranty

Three-year limited warranty.



Height	Length	EPA
17" (43 cm)	39 1/4" (100 cm)	2.46 sq. ft.