



Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering Guide

Example: DB14 A A0 12L E

Product Code	DB14	LED Bollard
Finish	A H	Black Bronze
Optics	A0	Symmetric
Wattage	12L	9.5W LED
Voltage	E	120V

Specifications

HOUSING:

360 low-copper die-cast aluminum alloy . Dome roof with die-cast aluminum louvers. Easy access to lamp. 5" dia. extruded aluminum with a wall thickness of 0.125". All non-ferrous fasteners prevent corrosion and ensure longer life.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

OPTICAL ASSEMBLY:

Symmetric. Die-cast aluminum louvers with underside painted with highly reflective white powdercoat. Tempered glass globe.

LAMPING:

9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. 2700K warm white delivers 800 lumens. Lamp life is rated at 25,000 hours. 120 volt only.

ELECTRICAL ASSEMBLY:

Ballast assembly is mounted to an aluminum plate, which is mounted inside the base. Quick disconnects for easy installation and removal.

INSTALLATION & MOUNTING:

Tube is mounted to the base plate with three (3) 5/16-18 flat head allen key stainless steel tamper-resistant screws.

WARRANTY:

Five-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height :

14" (36cm)

Bolt Circle:

3" (8 cm)

Base Diameter:

5" (13cm)

Width:

6" (15cm)

Anchor Rods:

Internal (3) 3/8" dia. x 8" long (1 cm x 20cm)

Max. Weight:

Powdercoat: 10 lbs

