

CHLORIDE

by Signify



Exit/Emergency

Caliber series

Architectural LED edge-lit
special wording sign



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Example: CSBR2RE17

CS

Series

CS - Caliber Series White LED AC Only Signage

Housing Color

A - Brushed Aluminum
B - Black
W - White
BR - Dark Bronze

of Faces

1 - Single Face
2 - Double Face

Graphics Color

R - Red
G - Green
B - Blue
K - Black
Y - Yellow

Optional text colors available, consult factory.

Lens Insert

Blank - Clear
M - Mirror

Special Wording

See Back Page or Consult Factory

Options

Blank - No Options
FL - AC Flasher
RFL - Remote Switched Flasher

Accessories (Order Separately)

PKIT12W - Pendant Kit, 12" White Finish*

PKIT12B - Pendant Kit, 12" Black Finish*

*Custom pendant lengths and colors available, consult factory.

codes and standards

- UL 48 listed
- IC rated
- UL damp location listing 32°F (0°C) to 104°F (40°C)
- Meets ADA specifications for wall mounted lighting fixtures

construction

- All housing components are premium die-cast aluminum construction.
- A range of finishes are available (see Ordering Information below).
- A bar hanger bracket kit is standard for recessed applications.

installation

- Universal mounting configurations include recessed ceiling mount, surface ceiling mount, surface end mount and surface wall mount.
- Surface mount configurations mount to a 3.5" octagonal junction box.

electronics

- AC only - 120/277 VAC dual voltage input with surge protection is standard on all models.

operating temperature range

- 32°F (0°C) to 104°F (40°C).

power consumption

- AC only, 120 VAC: 60 Hz, 0.084 A, 9.1 W, .90 Pf.
- AC only, 277 VAC: 60 Hz, 0.037 A, 9.3 W, .90 Pf.

lamps

- Illumination of the Caliber Signage panel is accomplished with the use of high-brightness white LEDs in an optical array offering even illumination.

warranty

- Five full year warranty on unit.




CS Caliber series architectural LED edge-lite special wording sign

options

- FL – This option enables the sign to operate in a 50% duty cycle flashing mode any time AC power is present. This option allows off or flashing operation.
- RFL – This option allows for an external, normally open, dry contact switch to control the flashing mode. This mode allows for off, on, or flashing operation.

dimensions

6" surface ceiling mount



See Caliber Series for more dimensions and mounting examples.

special wording examples (consult factory for additional options)



E2



E4



E6



E8




E11



E14




E16



E17



E24




E25



E26




E27



E28



E29



E30

