

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_


Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

### Ordering Guide

Example: PTW3080 F2 A

<b>Product Code</b>	PTW3080	Wall Mount
<b>Fixture Mounting</b>	F2 F3	2 3/8 Tenon 3" Tenon
<b>Finish</b>	A B H I G J	Black White Bronze Gray Verde Green



### Specifications

**HOUSING:**

6061-T6 Extruded Aluminum.

**FINISH:**

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

**WARRANTY:**

Three-year limited warranty.

**Height :**

10 1/4" (26.035 cm)

**Length:**

18" (45.72 cm)

**EPA:**

.48

