

Combines **flexibility and** precision

The **Philips Lumec Zenith LED post top luminaires** have many features that allow its appearance to be customized and personalized. By combining high-tech technology with elements of modern design, the Zenith luminaires give you great flexibility and freedom. The Zenith was specially developed for lighting large areas, such as parks, public areas, and entryways. Powered by the Philips EcoSwap LED light engine, Zenith provides longevity and energy savings.

Zenith LED luminaires

The Philips Lumec Zenith LED post top luminaires have many features that allow its appearance to be customized and personalized.

Prior to ordering, consult specification sheets for the most current information, notes, and exclusions.



Lumen range: 4,201-6,995 Wattage range: 50, 70 Efficacy range: 82-108




Benefits

- Wide selection of options and styles for greater design freedom.
- Prismatic globe provides excellent pole spacing.
- Powered by the Philips EcoSwap LED light engine providing longevity and energy savings.
- Lumen packages with output of up to 6,995 lumens.
- Type 3 and 5 optics available.
- Color temperatures 4000K and 3000K are available.




Dimensions



Z14: EPA: 2.4 sq. ft. Weight: 27 lbs (12.3 kg)



Z12: EPA: 2.0 sq. ft. Weight: 19 lbs (8.6 kg)



Z40: EPA: 2.3 sq. ft. Weight: 26 lbs (11.8 kg)



Z12A: EPA: 1.8 sq. ft. Weight: 18 lbs (8.2 kg)



Z47A: EPA: 2.3 sq. ft. Weight: 26 lbs (11.8 kg)

© 2018 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd. 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008