



Ordering guide

Example: HFP310 P4 A N PM

Product Code	Post Diameter	Finish	Arm Accessory	Post Matching
HFP310			N	PM
HFP310 Single	P4 4" Post Mount	A Black B White G Verde H Bronze I Gray J Green	N None	PM Post Matching

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Specifications

Housing

6063-T6 Extruded aluminum.

Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

Warranty

Three-year limited warranty.

Height	Length	EPA
39 1/2" (100 cm)	45 3/4" (116 cm)	3.05 sq. ft.

Internal Slip Fitter Height

15 1/2" (39 cm)

Internal Slip Fitter Diameter

3 1/2" (9 cm)

