

Project: \_\_\_\_\_


Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_



### Ordering Guide

Example: HFP310 P4 A N PM

<b>Product Code</b>	HFP310	Single
<b>Post diameter</b>	P4	4" Post Mount
<b>Finish</b>	A B G H I J	Black White Verde Bronze Gray Green
<b>Arm Accessory</b>	N	None
<b>Post Machining</b>	PM	Post Machining

### Specifications

**HOUSING:**  
6063-T6 Extruded aluminum .

**FINISH:**  
Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

**WARRANTY:**  
Three-year limited warranty.

**Height :**  
39 1/2" (100 cm)

**Length:**  
45 3/4" (116 cm)

**Internal Slip Fitter Height:**  
15 1/2" (39 cm)

**Internal Slip Fitter Diameter:**  
3 1/2" (9 cm)

**EPA:**  
3.05 sq. ft.

