

Project: _____

Location: _____

Cat.No: _____

Type: _____


Lamps: _____ Qty: _____

Notes: _____

Ordering Guide

Example: 78 ABS

Product Code	78	Refractor
Finish	ABS	Antique Brass
	ACP	Antique Copper
	ARD	Antique Red
	ASI	Antique Silver
	BLK	Black
	BRN	Brown
	BRZ	Bronze
	FGN	Forest Green
	GRA	Granite
	IRN	Ironstone
	RBZ	Rustic Bronze
	SRT	Shadow Rust
	VBZ	Verde Bronze
	VCP	Verde Copper
	VGN	Verde
	VTC	Vintage Copper
	WBZ	Weathered Bronze
	WHT	White



78 Accessories

Refractor

Specifications

CONSTRUCTION:

Cast aluminum 4 5/16" dia. ring.(Unpainted.) Two (2) 4 1/2" dia. black neoprene gasket. 6" Type V Glass Refractor. Cast aluminum refractor support. (Painted)

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

Height:

13 7/8"

Width:

6 1/4"

