



Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering Guide

Example: CUL6 S7 LED2W _

Product Code	CUL6	Copper Pathlyte	
Mounting	S7	Mounting Stake	*1
LED	LED2W	LED Lamp	
Finish	_	Natural Copper	*2

*1 Mounting stake option only available with Natural Copper Pathlyte.
 *2 When ordering Natural Copper, product code will read as CUL6.

Specifications

HOUSING:

Spun solid copper roof with copper stem. Machined brass threaded adapter for tool-less relamping. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

FINISH:

Natural Copper is bright polished, untreated copper. Color will age naturally to a fine dark copper patina.

OPTICAL ASSEMBLY:

Reflective white powdercoat on underside of roof. Frosted tempered glass lens.

LAMPING:

Philips 12V LED 1.2W Capsule lamp. Up to 88% energy savins when compared to a 10W Capsule halogen lamp. Long lifetime of 15,000 hours (B50,L70). Operating temperature range is between -20C and 35C (ambient). Suitable for use in enclosed luminaires where the case temperature (Tc) remains below Tc MAX. Total Lumens = 105lm Lamp is included with fixture. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

Bi-pin socket type (G4) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

WARRANTY:

5 year extended warranty

CERTIFICATIONS:

Manufactured to ISO 9001:2008 Standards. ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations.

CUL6 Copper Path light

LED Accent

Specifications

Height :
16 1/4" (413mm)

Width:
6" (152mm)

Max. Weight:
2.75 lb

