

Day-Brite CFI

by  Signify

Healthcare

RelaxView LED Graphic
Wall Illuminator

4200K



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Day-Brite / CFI RelaxView LED Graphic Wall Illuminators are designed specifically to optimize the illumination of graphic images. Its unique side hinge enables easy graphics change-out. The thin profile provides a contemporary look and meets ADA standards. A relaxing environment is provided by clean aesthetics and soft uniform light appearance, helping patients feel more comfortable, calm, and at ease during imaging experiences.

Wall Illuminator ordering guide

example: RVGW024024-42-B

Model Number ¹	LED Color Temp.	Finish ²
—	42 —	
RVGW024024 24x24 nominal RVGW024048 24x48 nominal RVGW048048 48x48 nominal RVGW048060 48x60 nominal	42 4200K	B Black S Silver CC Custom Color

Footnotes:

- ¹ See page 2 for details. Custom sizes are available upon request.
- ² Customer to provide color chip to match.



RVGW Relaxview Graphic Wall Illuminator

4200K


Features

- Easy installation and requires minimal maintenance.
- Long life LED source.
- Available in neutral white 4200K.
- RelaxView dimmers available for dimming applications.
- Designed for wall mounting.
- Agion® antimicrobial finish.
- Class 1 low voltage installation.
- Dimming option available on RelaxView Power Distribution Module PDM.
- On/Off and 5 level dimming control available with addition of RelaxView Intelligent Wall Dimmer IWD.

Specifications

- **Construction:** Non-ferrous construction. Extruded aluminum housing with a 1/8" white acrylic lens.
- **Finish:** The housing has a polyester powder-coat paint finish with an Agion® antimicrobial finish.
- **Light Source:** LED source densely populated for lower power consumption and uniformity, attached to heat-sink for maximum performance and reliability. The LED source is available in 4200K white.
- **Electrical:** RelaxView is powered by remote Class 1 low voltage power distribution module(s) (sold separately). Dimming is available. The RelaxView panels do not include a DC power supply. Remote modular Power Distribution Module PDM needed with or without dimmer.
- **Installation:** Easy installation into standard grid or hard ceilings.
- **Listing:** Components are CE or ETL listed and RoHS compliant.
- **Warranty:** Fixture warranted against defects for 5 years from original date of purchase.

Dimensions (see chart below for details)



Model No.	Nominal Size (LxW) ¹	Visual Opening (in inches)		Graphic Size (in inches)		Light Box Dimensions (O.D. in inches)			Number of LEDs	Power (W) @24VDC	Current (A) @120VAC	Lum. Flux lm	Illum. Area Sq. In.
		Vert.	Horiz.	Vert.	Horiz.	Vert.	Horiz.	Depth					
RVGW024024	24x24	24.00	24.00	25.00	25.00	25.50	25.50	2.00	576	46.08	0.38	2304	576
RVGW024048	24x48	24.00	48.00	25.00	49.00	25.50	49.50	2.00	1152	92.16	0.77	4608	1152
RVGW048048	48x48	48.00	48.00	49.00	49.00	49.50	49.50	2.00	2304	184.32	1.54	9216	2304
RVGW048060	48x60	48.00	60.00	49.00	61.00	49.50	61.50	2.00	2880	230.40	1.92	11520	2880


Footnotes:

¹ Other sizes are available. Contact factory for pricing.

RVGW Relaxview Graphic Wall Illuminator

4200K

Scene choices



Wall Scene ordering guide

example: GDH2027-BCA

Scene Number ¹	Graphic Protection
—	<input type="checkbox"/> BCA —
GDH2027 Clouds FDL3098 Tropical FDL3139 Desert FDL3798 Garden FDL3015 Landscape FDL3022 Miscellaneous XXXXXXXX TBD	BCA Back, clear acrylic

Footnotes:

¹ Other scenes available upon request.

