

HADCO

by  Signify

Outdoor

TXF9

LEDGINE Teardrop



Sustainability embodied

Hadco's TXF9 LED teardrop seamlessly replaces HID technology while maintaining that traditional "teardrop" look. The Teardrop uses latest LED technology which maximizes energy savings and lowered maintenance cost to reduce your total cost of ownership. By combining modern LED technology and traditional design, the Teardrop LED luminaires are perfectly suited for several applications including residential streets, city streets, campuses, parking lots and retail centers.



LEDGINE TXF9

Teardrop

Product description

The Hadco TXF9 teardrop is an excellent solution for LED outdoor lighting. This teardrop uses the LEDGINE platform which maximizes energy savings and provides uniform and comfortable white light. The design and performance work in several applications including residential streets, city streets, campuses, parking lots and retail centers. The TXF9 is a great solution for new installations or replacing a variety of HID sources.

External features and benefits

(N) cast neck or (P) pipe threaded mounting options

Low-copper cast aluminum housing

Two globe options: (GF) Flat Glass (KL) Long Acrylic

ORT technology (optical rib technology) globe




Internal features and benefits

10kV / 10kA surge suppression (optional) <3kV built into drivers.

Programmable 0 - 10V dimming module (optional).

120 - 277VAC or 347 - 480VAC driver, 530 mA, 50/60 Hz auto-sensing.



Low-copper die-cast heat sink and lens frame.

Multiple distribution options. (Type II, III, IV or V)

Precision designed, injection molded acrylic optic plate. IP66 optics chamber.

Tempered glass lens.

Multiple color temperatures. (3000K, 4000K, 5700K)


40, 64 or 80 LED options.

Specifications




TXF9 (GF) Flat Glass

Dimensions - 23 13/16" (H) x 18 3/8" (W)
Weight - 25 lbs
EPA - 2.00 sq. ft.



TXF9 (KL) Long Acrylic

Dimensions - 37 7/8" (H) x 18 3/8" (W)
Weight - 32 lbs
EPA - 2.60 sq. ft.



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

