





Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

Ordering guide

Sample #: RGLOLEDR (Housing) PG1RCRW (Panel/Face Plate)

Family		Battery	LED Color	Housing Color
RGLO SGLO	Edge-Glo Recessed Ceiling Housing Edge-Glo Surface Housing	LED - AC Only, LED LEDX - Nicad Battery LED	R - Red LEDs	(blank) If specifying RGLO Model¹ W White B Black SS Brushed Stainless Steel

Each exit sign requires 2 separate catalog numbers when ordering. (eg: SLGOLEDRW for the Housing and a PG1RCRW for the Panel/ Face Plate)

Accessories³ (Order Separately)

WSC12 - White stem (12") & canopy for surface housing²

 $\textbf{WSC24} \quad \text{- White stem (24") \& canopy for surface housing}^2$

WSC36 - White stem (36") & canopy for surface housing² $\textbf{BSC12} \quad \text{-} \; \text{Black stem (12") \& canopy for surface housing}^2$

BSC24 - Black stem (24") & canopy for surface housing²

BSC36 - Black stem (36") & canopy for surface housing²

Footnotes

- ¹ RGLO recessed housing does not have a painted finish.
- $^{\rm 2}$ Custom pendant lengths and colors available, consult
- ³ Consult Signify to confirm whether specific accessories are BAA-compliant.

PGLO panels

Family PG	# of Faces	Letter/Background Colors ⁷	Directional Indicator	Faceplate Finish	Options
PG Edge-Glo Panel and Faceplate	1 Single Face 2 Double Face	RC Red on Clear ⁴ RW Red on White ⁵	Single Face EXIT Panels (blank) No Chevrons R Chevron Right L Chevron Left D Chevron Double Double Face EXIT Panels (blank) No Chevrons LR Left or Right Chevron D Chevron Double	W White B Black SS Brushed Stainless Steel	SW Special Wording ⁶ Refer to special wording legend for suffix for specific messages. For example: SW-E2. Message color is available in red, other colors must be specified.

Footnotes

- ⁴ Single face panels to have a clear background and double face panels will have a mirror separator.
- ⁵ Available on single or double face signs.
- $^{\rm 6}$ Special Wording is available (Refer to Special Wording legend).
- ⁷ EXIT Panels available with 6" letters only.



RGLO/SGLO Edge-Glo edge-lit LED exit sign

codes and standards

- · UL 924 Listed (AC only exits)
- ETL Listed to UL 924 Standards
- NFPA 101, NEC, IBC, BOCA, and OSHA illumination standard
- · DoE Compliant

construction

Recessed housings:

- 20 gauge galvanized steel with wiring access plate to allow electrical connection without removal of wireway.
- Standard housing is suitable for use in plenum ceilings.
- Vertically adjustable hanger bracket with proprietary Alkco-Loc bar hangers lock onto T-bar or can be supported from building structure. Bar hangers rotate 90°

surface housings

- 20 gauge cold rolled steel with universal mounting capability.
- KO pattern in top and end accommodates standard 1-device outlet box cover for installation without a canopy.
- Top, end and back KO pattern allows mounting with supplied canopy/mounting plate over 4" octagonal outlet boxes.
- Standard finish is white polyester resin powder coat.

panels/faceplates

- Injection molded clear acrylic panels with chamfered edges.
- Bottom edge is reflectorized to facilitate uniform illumination.
- Red letters and chevrons are reverse silk screened onto panels.
- Panels are pre-installed into a die-formed 18 gauge cold rolled steel face plate which attaches to housing with torsion springs.
- There are no exposed fasteners on faceplate.
- Standard faceplate finish is white polyester-resin powder coat.
- Optional Black finish and brushed stainless steel.

electronics

- · 120/277 VAC dual voltage input.
- Self-powered models include brownout detection, AC lockout, low voltage disconnect, AC power indicator and push-to-test switch.
- Operating temperature range: standard location listed: 77°F (25°C).

power consumption:

- AC only red: (120VAC) .034 A, PF = 0.96, (277VAC) .015 A, PF = 0.91.
- Emergency operation red: (120VAC) .043 A,
- PF = 0.95, (277VAC) .019 A, PF = 0.97.

lamps

 Illumination of the exit face is accomplished with long-lasting, high output red LEDs.


battery

- Maintenance free sealed nickel cadmium battery.
- Provides a minimum of 90 minutes of emergency power.

warranty


- Five full year warranty on electronics and unit.
- Nicad Battery: 3 year full with 7 year pro-rata.

Dimensions



RGLO/SGLO Edge-Glo edge-lit LED exit sign

Special Wording Examples (other options available)



Buy American Act of 1933 (BAA):

This product is manufactured in one of our US factories and, as of the date of this document, this product was considered a commercially available off-the-shelf (COTS) item meeting the requirements of the BAA. This BAA designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Prior to ordering, please visit www.signify.com/baa to view a current list of BAA-compliant products to confirm this product's current compliance.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The informatior presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.