

by (signify

Urban


Pole accessories


20-EXT Post top tenon

Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	



Example: 20-EXT ABS





Specifications

CONSTRUCTION:

Cast aluminum decorative fitter. Welded construction inside of outside tubing and fitter. 3" O.D. x .125" Wall tubing x 6 1/8" long. Set screws supplied. Tenon slips over Hanover Lantern 4" dia. x .125" Wall Fluted aluminum tubing (10 flutes.)

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

Height:

11 3/8"

Width: 7"



© 2019 Signify Holding. All rights reserved. This document may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners. Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008