

Stonco

by  Signify

Wall Mount

Low profile wall

PW15/PW30/PW50



Sleek & slim, with energy saving illumination

The Stonco LED Low profile wall provides efficacies up to 110 LPW, with significant energy savings over HID luminaires.

The Low profile wall features energy saving LED technology when you need a discreet way to illuminate outdoor areas. Low Profile Wall is available in three sizes to accommodate multiple mounting heights – 15, 30, and 50W, providing 50-100W HID equivalent illumination.


An ideal choice for any indoor or outdoor wall mounted application.




PW LED Low profile wall




- Budget-friendly, discreet fixture for a wide variety of outdoor spaces
- Energy efficient fixture that delivers up to 110 lumens per watt.
- 3 size options: 15, 30 or 50 watt.
- Slim profile, just over 4 inches.
- Quick and easy installation – mounts to a standard 3 1/2 or 4" junction box.
- Durable construction of die-cast aluminum with a UV stabilized lens and stainless steel hardware.
- 5 year limited warranty.



PW15
15W - 1656 Lumens



PW30
30W - 3090 Lumens



PW50
50W - 5114 Lumens

Ordering guide

Example: **PW-50-NW-G1-8-BZ**

Luminaire	Wattage	LED Color - Generation	Voltage	Finish
PW		NW-G1	8	BZ
PW Low Profile Wall	15 15W 30 30W 50 50W	NW-G1 Neutral White, 4000K, 80 CRI, Generation 1	8 120-277 Volts	BZ Bronze

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

