

Ledalite architectural recessed luminaires deliver the highest quality lighting solutions to satisfy your projects needs through innovative technologies and attention to detail.

Reference	
★ ★ ★	High applicability
★ ★	Medium applicability
★	Low applicability
-	Non-applicable



		\$		\$\$		\$\$\$	
Applications	Family	ArcForm Duo	Pique Duo	DecoForm	Shine	SilkSpace Definition	BloomBox
	Education	★ ★ ★		★ ★ ★	★ ★ ★		★ ★ ★
	Office	★ ★ ★		★ ★ ★	★ ★		★ ★ ★
	Healthcare	★ ★ ★		★ ★	★ ★ ★		★ ★
	Fashion and Retail	★ ★ ★		★ ★ ★	★ ★		★
	Design Ready, 10-Day QuickShip	Design ready – Quick Ship Guide		Design ready – Quick Ship Guide	Design ready – Quick Ship Guide		-
	Sizes	2x2, 2x4, 1x4		2x2	1x1, 1x2, 2x2, 2x4, 1x4, 20"x2', 20"x4', 20"x60" 30"x30" 600x1200mm, 750x750mm, 600x600mm, 300x1200mm, 300x600mm, 300x300mm		2x2
Features and Specifications	Watts (Max)	59		53	63		29
	lm/W (Max)	152		123	138		171
	Lumens (Max)	8000		6000	8000		5000
	IES TM-21-11 Lifetime	L ₇₀ >102,000 hrs		L ₈₀ >72,000 hrs	L ₈₀ >60,000 hrs		L ₇₀ >72,000
	Product Height	3–15/16" (4–11/16" @ Driver)		Recessed: 3–15/16" (up to 4–15/16" at driver) Supended: 5"	4–3/8"		2–1/5"
	Light Distribution	Batwing (MesoOptics) or Lambertian (Silk)		Lambertian (Silk)	Lambertian (Silk)		Batwing (Micro Cells)
	Spacing Ratio	10'x10' OC (Batwing) or 8'x8' OC (Lambertian)		8'x8' OC	8x8' OC		14'x14' OC
	CCT	Static: 2700K, 3000K, 3500K, 4000K, 5000K Tunable White: 2700K–6500K BioUp: 2700K–5000K (on request)		2700K, 3000K, 3500K, 4000K, 5000K	Static: 2700K, 3000K, 3500K, 4000K, 5000K Tunable White: 2700K–6500K (on request) BioUp: 2700K–5000K (on request)		Static: 3500K, 4000K
	CRI	90+		90+	90+		90+
	Ceiling Types	Compatible with 15/16" lay-in acoustical ceilings using exposed grid suspension (NEMA type G). For 9/16" slot T-grid ceilings, fixture will sit 5/16" above bottom of Tee. Integrated tabs are provided for different T-grid heights. Optional drywall kit trim mount					
	Housing Types	T-Grid, Drywall, & Chicago Plenum		T-Grid, Drywall, Chicago Plenum, & Suspended	T-Grid, Drywall, & Chicago Plenum		T-Grid & Drywall
	Emergency Options	Integral Battery Pack or GTD		Integral Battery Pack or GTD	Integral Battery Pack		-
	Service from Below	-		-			
	Optional Pre-Installed 6' Flex Whip						-
Integrated Controls	Interact Pro CS (Day/Occ)			-			
	Interact Pro RA (Radio Node)						-
	Interact Pro Enterprise SB (Day/Occ + IoT)			-			
	Lutron Athena and Vive				On request		-
Driver Options	Advance 0–10V						
	Advance DALI-2 D4i						-
	Advance Sensor Ready						
	Lutron Ecosystem LDE1						-
Certifications	IC Rating Direct Contact						
	DLC	V5.1 Standard & Premium		V5.1 Standard	V5.1 Standard & Premium		V5.1 Premium
	Declare						
Links	Spec Sheet						