



Add detail and style to any space with the Vetro accents and Calculite 4" LED downlights.

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

**Complete luminaire = Frame + Trim or Micro Vetro (optional) + Installation Accessories (if required)**

Note: This product is being phased out and is available only while inventory exists. Please review the Vetro 3D Printed element series for other available options. 3D Printed Vetro elements require a standard flanged trim whereas the D4A Vetro series requires a flangeless (F) trim.

### Decorative Element

example: D4A01 + C4RDL\_F + 4RN

Series	Model	Use with trim kit*	Use with frame-in kits
D4A Decorative Element - 4" Calculite LED - 4" Calculite CFL	02 Round acrylic	LED: C4RDL	LED: 4RN

\* Trim kit must be ordered separately. All combinations required the appropriate Calculite frame-in kit.

Specify Reflector separately. Flangeless trim required for Decorative element. Use specular clear (CL) finish for best performance.

### Features

**1. Decorative element:**

- (01) Solid high temp, UV resistant composite with open aperture, frosted interior diameter and polished exterior. Satin aluminum ring is mechanically inserted in composite to create drama and intrigue in the element.
- (02) Solid high temp, UV resistant composite with open aperture, frosted interior diameter and polished exterior. Machined facet along bottom edge.
- (03) Angled hand blown triplex glass carefully proportioned to each aperture size. Glass is gently and evenly illuminated for clean brightness recognition.
- (04) Cylindrical hand blown triplex glass carefully proportioned to each aperture size. Glass is gently and evenly illuminated for clean brightness recognition.

- 2. **Die cast construction ring:** Exterior edge of construction ring is visible, satin aluminum finish matches diameter of decorative element for a flangeless appearance. Aluminum die cast finish ring with crisp 90° edges conceals all fasteners for a clean finished appearance.
- 3. **Integral reflector:** 16 ga. aluminum, 50° visual cutoff to lamp and lamp image. Decorative Element is mechanically attached to reflector via die cast ring. Reflector is specular clear for best performance and aesthetics.
- 4. **Reflector:** Specified separately. Flangeless trim required. Use specular clear (CL) finish for best performance and aesthetics.
- 5. **Frame-in kit:** Specified separately. See frame-in kit specification sheet for details.

### Mechanical

Decorative element are mechanically secured to the die cast construction ring and the integral reflector from the factory.  
 Stamped aluminum cover ring provided on top of decorative element to cover construction ring fasteners.  
 Four #8-32 screws and 4 knurled die-cast thumb screws secure construction ring to frame in kit.

### Labels


cULus Listed.  
 Suitable for damp locations.



# D4A Vetro Accessory

Round decorative elements for Calculite LED 4"

## Dimensions



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008