


# Urban

P4130

**P4130** Pole





## **Ordering Guide**

Example: P4130 12 A T D

Product Code	P4130	
Pole Height	12 14 16 18	12' 14' 16' 18'
Finish	A B G H J	Black White Verde Bronze Green
Outlet Location (Optional)	Т	12" Down from Top - Aligned with House Side 4" Up from Top of Base - Aligned with House Side
Outlet Options (Optional)	D G	Standard Duplex GFI Duplex

### **Specifications**

#### HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy . 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel . Tenon is 356 HM sand cast aluminum.

#### FINISH

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

#### WARRANTY:

Three-year limited warranty.

#### OUTLET

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

# **P4130** P4130

## Pole

## **Specifications**

Tenon/Top:

3" OD

**Bolt Circle:** 

8" - 14"

**Anchor Rods:** 

(4) 3/4" dia. x 19"

**Base Dimensions:** 

19" dia. x 54 1/2"

Hand Hole:

6" x 11 1/2"

Shaft: 4" Straight

Wall Thickness:

0.125 Aluminum

Height:

12', 14', 16', 18'

## **Pole EPA Values**

#### Height

Windspeed(mph)	12'	14'	16'	18'
80	16.7400	10.9000	9.0700	7.5300
100	10.2600	6.4300	5.1300	4.0300

