



## Ordering guide

Example: HFP110 P4 A N PM

Product Code	Post Diameter	Finish	Arm Accessory	Post Matching
<b>HFP110</b>	<b>P4</b>		<b>N</b>	<b>PM</b>
HFP110 Single	P4 4" Post Mount	<b>A</b> Black <b>B</b> White <b>G</b> Verde <b>H</b> Bronze <b>I</b> Gray <b>J</b> Green	N None	PM Post Matching

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

## Specifications

### Housing

6063-T6 Extruded aluminum.

### Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

### Warranty

Three-year limited warranty.

Height	Length	EPA
35" (89 cm)	26 3/4" (68 cm)	1.40 sq. ft

### Internal Slip Fitter Height

19" (48 cm)

### Internal Slip Fitter Diameter

3 1/2" (9 cm)

