

**PHILIPS  
LUMEC**

Urban

Serenade DSX

S55 and S56



# Reliable efficiency, **designed for performance**

**Philips Lumec's Serenade DSX LED post top luminaires** are a beautiful staple of elegance and subtlety with a mighty and brilliant heart. It can be used to accentuate any environment no matter how harsh the prevailing conditions might be. The Serenade is a straightforward, no-nonsense luminaire, designed for performance and reliability.



S55



S55-CR55



S55C2



S56



S56C1

# Serenade

## Features and benefits

- Glass globe with no exterior prism
- Low uplight reduces light pollution
- Complete IP66 rated luminaire
- Multiple lumen packages with output of up to 10,885 lumens
- Type 2, 3, 4, and 5 optics available
- 4000K and 3000K color temperatures available
- Dimming driver standard
- Multiple driver options and programmed dimming options available

## Ordering guide: Luminaire

Series	LED module	Lamp type	Globe material	Optical system	Voltage	Driver options	Adaptors
<input type="text"/>	<input type="text"/>	<input type="text" value="T"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
<b>S55</b> Serenade DSX	<b>4000K</b> <b>35W32LED4K</b> <b>55W32LED4K</b>	<b>T</b>	<b>ACDR</b> Acrylic globe <b>GL</b> Glass globe	<b>LE2</b> Type II (ASYM) <b>LE3</b> Type III (ASYM) <b>LE3W</b> Type III (ASYM) wide <b>LE4</b> Type IV (ASYM) <b>LE5</b> Type V (SYMM)	<b>120</b> 120V <b>208</b> 208V <b>240</b> 240V <b>277</b> 277V <b>347</b> 347V <b>480</b> 480V	<b>AST</b> Pre-set, progressive start-up <b>CLO</b> Pre-set, manage lumen depreciation <b>DALI</b> Pre-set, compatible with the DALI control system <b>OTL</b> Pre-set to signal end of life of the lamp <b>DMG</b> 0-10V <b>CDMGP</b> Dimming level set by user <b>CDMGE25</b> 8 hrs. 25% reduction <b>CDMGE50</b> 8 hrs. 50% reduction <b>CDMGE75</b> 8 hrs. 75% reduction <b>CDMGM25</b> 6 hrs. 25% reduction <b>CDMGM50</b> 6 hrs. 50% reduction <b>CDMGM75</b> 6 hrs. 75% reduction <b>CDMGS25</b> 4 hrs. 25% reduction <b>CDMGS50</b> 4 hrs. 50% reduction <b>CDMGS75</b> 4 hrs. 75% reduction	<b>SFOK</b> Oak leaf fitter <b>SFX</b> Standard fitter
<b>S56</b> Serenade DSX	<b>3000K</b> <b>35W32LED3K</b> <b>55W32LED3K</b> <b>55W48LED3K</b> <b>72W32LED3K</b> <b>80W48LED3K</b> <b>108W48LED3K</b>						

Consult specification sheets for the S55C1-C2 and S56C1-C2 current information, notes, and exclusions.

## Ordering guide (continued)

Luminaire options	Poles & Brackets	Finish
<input type="text"/>	<input type="text"/>	<input type="text"/>
<b>BC</b> Block connector <b>BST</b> <sup>1</sup> Brass decorative cupola <b>BSTC</b> <sup>1</sup> Brass decorative cupola with clear coat <b>CPT</b> <sup>1</sup> Copper decorative cupola <b>CPTC</b> <sup>1</sup> Copper decorative cupola with clear coat <b>CR55</b> <sup>1</sup> Decorative crown <b>FN1</b> <sup>2</sup> Decorative finial <b>FN2</b> Decorative finial <b>FN3</b> Decorative finial <b>FN4</b> Decorative finial <b>FN6</b> <sup>2</sup> Decorative finial <b>FN8</b> Decorative finial <b>FN9</b> Decorative finial <b>FN10</b> Decorative finial <b>FN11</b> Decorative finial <b>FNC</b> Finial painted copper <b>HS</b> House Side Shield <b>OVR</b> Override function <b>PH8</b> Photoelectric cell <b>PH9</b> Shorting Cap <b>PHXL</b> Photoelectric cell, extended life <b>RC</b> Receptacle 3 pins <b>SP2</b> Surge protector <b>TN2.875C</b> 2 7/8" dia. Tenon adaptor <b>TN3</b> 3" dia. Tenon adaptor <b>TN3.5</b> 3 1/2" dia. Tenon adaptor	Consult Philips.com/luminaires for details and the complete line of Philips poles and brackets.	<b>BE2TX</b> Textured midnight blue <b>BE6TX</b> Textured ocean blue <b>BE8TX</b> Textured royal blue <b>BG2TX</b> Textured Sandstone <b>BKTX</b> Textured black <b>BRTX</b> Textured bronze <b>GN4TX</b> Textured blue green <b>GN6TX</b> Textured forest green <b>GN8TX</b> Textured Dk forest green <b>GNTX</b> Textured green <b>GR</b> Gray sandtex <b>GY3TX</b> Textured medium grey <b>NP</b> Natural aluminum <b>RD2TX</b> Textured burgundy <b>RD4TX</b> Textured scarlet <b>TG</b> Hammertone gold <b>WHTX</b> Textured white

1. S55 only      2. S56 only

## S55

**Lumen range:** 3,498 - 10,885  
**Wattage range:** 35 - 108  
**Efficacy range:** 86 - 111lm/W  
**EPA:** 2.6 ft² max.  
**Weight:** 63 lbs (28.58kg) max.

## S56

**Lumen range:** 3,498 - 10,885  
**Wattage range:** 35 - 108  
**Efficacy range:** 86 - 111lm/W  
**EPA:** 2.37 ft² max.  
**Weight:** 71 lbs (32.31kg) max.

Prior to ordering, consult specification sheets. Please visit [www.philips.com/luminaires](http://www.philips.com/luminaires) for the most current information, notes, and exclusions.

© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation  
 200 Franklin Square Drive, Somerset, NJ 08873  
 Tel. 855-486-2216

Philips Lighting Canada Ltd.  
 281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
 Tel. 800-668-9008