



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering Guide

Example: MUL5 A

Product Code	MUL5	Aluminum Pathlyte
Finish	A H G	Black Bronze Verde

Specifications

HOUSING:

Die-cast aluminum. Stem is extruded aluminum. Roof has dual stainless steel hinge with stainless steel spring-lock for tool-less entry and relamping. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

OPTICAL ASSEMBLY:

Spun aluminum reflector with white thermoset powdercoat. Frosted tempered glass sprinkler shield includes top and bottom silicone gaskets for tight seal.

LAMPING:

35W maximum T3 halogen. Lamp is included with fixture. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

Bi-pin socket type (G4) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height :	Width:	Max. Weight:
25" (635mm)	9" (229mm)	5.55 lb.

