

# HADCO

by  Signify

## Urban

### Arm bracket


### HFH2420 Twin

Project: \_\_\_\_\_  
Location: \_\_\_\_\_  
Cat.No: \_\_\_\_\_  
Type: \_\_\_\_\_  
Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
Notes: \_\_\_\_\_

### Ordering Guide

Example: HFH2420 P4 A

<b>Product Code</b>	HFH2420	Twin
<b>Post diameter</b>	P4	4" Post Mount
<b>Finish</b>	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green



### Specifications

#### HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy .

#### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

#### MOUNTING:

Cast Aluminum Hub mounts to a 3" OD x 3" long (P3) [if applicable] or 4" OD x 6 1/2" long (P4) [if applicable] tenon and is secured with at least (3) 5/16"-18 stainless steel set screws.

#### CERTIFICATIONS:

Manufactured to ISO 9001:2008 Standards.

#### WARRANTY:

Three-year limited warranty.

#### Height :

17" (43 cm)

#### Length:

46 1/2" (118 cm)

#### EPA:

2.25 sq. ft.