

High
performance
never looked
better.

Sleek and lightweight with a robust 145 Lumens per watt,
Day-Brite / CFI brings you the HBY high bay.

Day-Brite
CFI
by @signify

Industrial

HBY high bay

@signify

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

PDb-1816LL 02/19 www.day-brite.com

Signify North America
Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008



Lighting that
makes your
space & you
look great

Big box doesn't have to mean big budget...

It doesn't have to mean clunky either... With a durable, sleek, modern design and a great pricetag, the HBY high bay will help make your spaces look fantastic and impress your clients.

HBY is an ideal choice for applications where you need powerful illumination combined with visual comfort due to high traffic volumes — like large retail or higher educational spaces.

Installation is a breeze with a variety of mounting accessories available, however the long life and reliability of these luminaires means you won't have to think about that for a long time.

- Key benefits for your projects:
- Lower energy costs
 - Ease of installation and use
 - Proper code and safety compliance
 - Robust system for demanding installations
 - Comfortable, well-lit space for occupants
 - Cosmetic appeal for aesthetically important environments
 - Robust Specs: cETLus, DLC, DLC Premium, IP65, wet location and NSF certifications
 - Up to 145 LPW




up to
145_{LPW}

Ordering guide

Example: HBY24L840-UNV-M-WT

Family	Lumens (nominal) ¹	Color Temperature	Voltage	Distribution	Paint Colors	Options
HBY						
HBY	12L 12,000 lumens	835 3500K (CRI 80)	UNV Universal voltage 120-277V	N Narrow	BZ Dark Bronze	WP6 ⁴ Wired 6' 16/3 Cord & NEMA Twist Lock Plug
	18L 18,000 lumens	840 4000K (CRI 80)	120 120V	M Medium	WT White	WP6D ⁴ Wired 6' 16/3 Cord & NEMA Twist Lock Plug for Line Voltage and Wired 6' 16/3 Cord & Plug for Dimming Control
	24L 24,000 lumens	850 5000K (CRI 80)	208 208V	W Wide	BK Black	WC6D Wired 6' 16/3 Cord for Line Voltage and Wired 6' 16/3 Cord for Dimming Control
	30L ² 30,000 lumens		240 240V	A Aisle	AL Silver Aluminum	BSL10LST Factory wired Philips Bodine integral emergency pack, nominal 1100 to 1400 lumens
	36L ² 36,000 lumens		277 277V			MD360W Wet location occupancy sensor (ON/OFF)
			347 ^{2,3} 347V			MD360WD Wet location occupancy sensor (ON/DIM)
			480 ^{2,3} 480V			SWIDT SpaceWise motion detector
						FGS Solite stippled tempered glass lens

(Factory wired 6' 16/3 black cord is standard)



Footnotes

- ¹ Nominal delivered lumens at 25°C ambient
- ² Not available with BSL10LST option
- ³ Not available with 30,000 or 36,000 lumens
- ⁴ Must specify line voltage

