


eColor Cove MX Powercore

Premium interior linear LED cove and accent luminaire with solid color light

Date: _____
 Type: _____
 Firm Name: _____
 Project: _____

eColor Cove MX Powercore delivers the highest light output in the line of solid color linear cove lights from Color Kinetics. With medium and wide beam angles and a range of fixed colors, luminaires can be used for accent lighting as well as wall and ceiling cove applications. Offers environmentally conscious buyers a green, energy-efficient lighting solution without sacrificing quality or quantity of light.

- Integrates patented Powercore technology—Powercore rapidly, efficiently, and accurately controls power output to luminaires directly from line voltage, eliminating the need for external power supplies and allowing long product runs. Contractor-friendly installation dramatically simplifies installation and lowers total system cost.
- Support for multiple voltages—Accepts line voltage input of 100 to 277 VAC for consistent installation and operation in a variety of locations.
- Dimming capability—Patented DIMand technology offers smooth dimming capability with selected commercially available reverse-phase ELV-type dimmers.



[Product page](#)

Beam Angle	50° x 70°, 125° x 120°
LED Channels	Red, Green, Blue, or Amber

Input Voltage	100 to 277 VAC, auto-ranging, 50/60 Hz
Housing Material	Die-cast aluminium, white powder-coated finish
Approbations	UL/cUL, FCC Class B, CE, C-Tick, CCC, SAA
Environment	IP20
Applications	Cove Lighting

Specification Sheets

PDF Download	Beam Angle	Power	Weight	Item Number	12NC
Red, 50° x 70° Beam Angle, 305 mm (1 ft)	50° x 70°	12.5 W	454 g (1 lb)	223-000050-08	910503701112
Red, 50° x 70° Beam Angle, 1.2 m (4 ft)	50° x 70°	50 W	2 kg (4.41 lb)	223-000050-20	910503702595
Red, 125° x 120° Beam Angle, 305 mm (1 ft)	125° x 120°	12.5 W	372 g (0.82 lb)	223-000050-12	910503701730
Red, 125° x 120° Beam Angle, 1.2 m (4 ft)	125° x 120°	50 W	1.8 kg (3.97 lb)	223-000050-16	910503702591
Green, 50° x 70° Beam Angle, 305 mm (1 ft)	50° x 70°	12.5 W	454 g (1 lb)	223-000050-09	910503701113
Green, 50° x 70° Beam Angle, 1.2 m (4 ft)	50° x 70°	50 W	2 kg (4.41 lb)	223-000050-21	910503702596
Green, 125° x 120° Beam Angle, 305 mm (1 ft)	125° x 120°	12.5 W	372 g (0.82 lb)	223-000050-13	910503701731
Green, 125° x 120° Beam Angle, 1.2 m (4 ft)	125° x 120°	50 W	1.8 kg (3.97 lb)	223-000050-17	910503702592

For help estimating the light output and distribution of eColor lighting luminaires, please contact Color Kinetics Applications Engineering Services at <http://www.lighting.philips.com/support/connect/contact-us>.



Specification Sheets

PDF Download	Beam Angle	Power	Weight	Item Number	12NC
Blue, 50° x 70° Beam Angle, 305 mm (1 ft)	50° x 70°	12.5 W	454 g (1 lb)	223-000050-10	910503701114
Blue, 50° x 70° Beam Angle, 1.2 m (4 ft)	50° x 70°	50 W	2 kg (4.41 lb)	223-000050-22	910503702597
Blue, 125° x 120° Beam Angle, 305 mm (1 ft)	125° x 120°	12.5 W	372 g (0.82 lb)	223-000050-14	910503701732
Blue, 125° x 120° Beam Angle, 1.2 m (4 ft)	125° x 120°	50 W	1.8 kg (3.97 lb)	223-000050-18	910503702593
Amber, 50° x 70° Beam Angle, 305 mm (1 ft)	50° x 70°	10 W	454 g (1 lb)	223-000050-11	910503701115
Amber, 50° x 70° Beam Angle, 1.2 m (4 ft)	50° x 70°	40 W	2 kg (4.41 lb)	223-000050-23	910503702598
Amber, 125° x 120° Beam Angle, 305 mm (1 ft)	125° x 120°	10 W	372 g (0.82 lb)	223-000050-15	910503701733
Amber, 125° x 120° Beam Angle, 1.2 m (4 ft)	125° x 120°	40 W	1.8 kg (3.97 lb)	223-000050-19	910503702594



© 2019 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics
www.colorkinetics.com/ls/essentialcolor/eccovemxpc/