LUMEC

by (s) ignify

RoadFocus

RFS/RFM/RFL Cobra head



Enhance your roadways

Lumec RoadFocus cobra heads are designed to replace 70-400W HID luminaires and provide uniform, high performance LED illumination.

With RoadFocus, your city or town will enjoy well-lit roadways and an increased sense of security that extends from small alleys to multi-lane expressways.


Benefits

- Update your lighting infrastructure with money-saving upgrades from HID to LED Roadway lighting.
- Consistent, familiar aesthetics by day, with powerful brilliant white LED illumination at night.
- Seamless integration in new and existing installations across all roadway applications.
- Full range of optics provide uniform illumination designed specifically for a wide range of roadway applications.
- LED technology provides an increased system life and minimizes energy consumption for an expedited return on your investment.
- Broadest set of stand-alone to connected LED Roadway lighting controls solutions available to further customize your lighting

 now or in the future.
- Includes Service Tag, an innovative way to provide assistance throughout the life of the product.

RFS/RFM/RFL RoadFocus

Cobra head



Applications

· Multi-lane Freeways and Expressways

· Maior Roads

· City Streets

· Collector Roads

· Intersections

· Adjoining Roadways

· Bridges and Overpasses

· Local Roads

· Residential Streets

Alleys

Technical features

Note: Prior to ordering, consult specification sheets on signify.com/prolighting for the most current information, notes and exclusions.

Type II Short, Type II Medium, Type III Short, Optics:

Type III Medium, Type IV, Type V

Color temperature: 4000K, 3000K and 2700K

Luminous flux: Approx. 1,600 to approx. 44,000 Lumens

Efficacy: up to 156 LPW Uplight: U0 = No uplight

Luminaire Up to 100,000+ hours with >L₇₀ at 25°C

Useful Life: (includes LEDs and drivers)

Connected Lighting

Interact City, SR Sensor Ready, DALI, FAWS & Controls Solutions:

Driver: 0-10V Dimming Driver Standard

Power: 14W to 340W (steady state in W, +/- 10%)

Surge protection: SP1 standard, SP2 option provides extra surge protection

Twist-Lock receptacle: 7-pin standard, 5-pin optional Finish: Grey, White, Black, Bronze

IP Rating: IP66 rated light engines

Material: Low copper die cast aluminum housing and door

Meets ANSI C136.31-2018 3G rating for bridges and overpasses Vibration:

Mounting: Fits on 1.66" O.D. (1.25" NPS), 1.9" O.D. (1.5" NPS) or $2^3/8$ " O.D. (2" NPS) tenon. Tilt +/-5° by steps of 2.5°.

Light Trespass


Cul-de-Sac, Front Side, House Side, Left Side, Right Side **Shielding Options:**

10-year limited warranty. Warrantv:


See signify.com/warranties for details and restrictions.

Dimensions

RoadFocus Small (RFS)




Bottom View



Weight: 9.4 lbs EPA: 0.52 sq. ft.


RoadFocus Medium (RFM)






Weight: 12.2 lbs EPA: 0.53 sq. ft.

RoadFocus Large (RFL)





Weight: 27.3 lbs EPA: 0.92 sq. ft.



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify Canada Ltd. 281 Hillmount Road,