

## Ordering guide

Example: HFH2610 P4 A

Product Code	Post Diameter	Finish
<b>HFH2610</b>		
HFH2610 Single	P4 <sup>1</sup> 4" Post Mount	<b>A</b> Black <b>B</b> White <b>G</b> Verde <b>H</b> Bronze <b>J</b> Green

1. Recommended tenon size of 4" dia. x 6 1/2" length

## Specifications

### Housing

356 HM high-strength, low-copper, proprietary cast aluminum alloy.

### Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

### Mounting

Cast Aluminum Hub mounts to a 3" OD x 3" long (P3) [if applicable] or 4" OD x 6 1/2" long (P4) [if applicable] tenon and is secured with at least (3) 5/16"-18 stainless steel set screws.


### Certifications

Manufactured to ISO 9001:2008 Standards.

### Warranty

Three-year limited warranty.

Height	Length	EPA
27 1/4" (69 cm)	26 3/4" (68 cm)	1.90 sq. ft.



Project:

Location:

Cat.No:

Type:

Lamps:

Qty:

Notes: