

# Stonco

by @ignify

Floodlights

General purpose floods

FL20/40/80/150/200/300



## Versatile & stylish for a wide range of applications

The Stonco LED General purpose floodlights offer energy saving LED technology for long life and reduced maintenance.



### Loads of options

With five complementary sizes to choose from, these floodlights provide uniform illumination, simplified installation, and a rugged robust design. Mounting is made easy with flexibility for ground mount, wall mount, or pole mount installations. They are an ideal choice for sign lighting, building facades, security lighting, and general purpose floodlighting applications.

Energy savings don't get better than this – up to 79% savings compared to HID\*.


\* Based on comparison between 150W PSMH luminaires (at 190W) and FL40-NW-G1-K-FL-8-BZ (at 39W).



# FL General purpose floods



- Complete family of LED floodlights ideal for illuminating signs, building facades or other dark areas.
- Can be mounted on the ground, wall, or pole-mounted.
- Discreet and modern design
- All sizes arrive fully assembled and ready to install. Three larger sizes have a trunnion or slip fitter mount and the two smaller sizes have a knuckle mount.
- Fade-resistant, textured bronze finish with tempered glass lens that is heat and impact resistant.
- IP66 rated.
- 5 year limited warranty.



## Ordering guide

Example: **FL150-NW-G1-PCB-T-FL-8-BZ**

Luminaire	LED Color	Generation	Options	Mounting	Distribution	Voltage	Finish
<input type="text"/>	<input type="text" value="NW"/>	<input type="text" value="G1"/>	<input type="text"/>	<input type="text"/>	<input type="text" value="FL"/>	<input type="text" value="8"/>	<input type="text" value="BZ"/>
<b>FL20</b> LED Floodlight 20W	<b>NW</b> Neutral White 4000K, 80CRI	<b>G1</b> Generation 1	<b>Blank</b> None <b>PCB<sup>1</sup></b> With Photocell	<b>K<sup>2</sup></b> Knuckle Mount ½" NPS male	<b>FL</b> Flood	<b>8</b> 120-277VAC	<b>BZ</b> Bronze
<b>FL40</b> LED Floodlight 40W				<b>T<sup>3</sup></b> Trunnion Mount			
<b>FL80</b> LED Floodlight 80W				<b>S<sup>4</sup></b> Slip Fitter Mount			
<b>FL150</b> LED Floodlight 150W							
<b>FL200</b> LED Floodlight 200W							
<b>FL300</b> LED Floodlight 300W							

1. Photocell available with FL20, FL40, FL80, and FL150 only. Knuckle and Trunnion Mount only. **2 K** Knuckle Mount only available with FL20 and FL40.

3. **T** Trunnion Mount only available with FL80, FL150, FL200 & FL300. **4. S** Slip Fitter Mount only available with FL80, FL150, FL200 & FL300.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

