Downlighting

LIGHTOLIER

by (signify

Calculite LED

C3R/C3S Round & Square



More choices than ever before for no-limits lighting design

You love to light, layer and illuminate spaces that make a statement. You've been asking us for more options, a smaller aperture, one-frame... well, we listened.

All luminaires feature:

- New 3" aperture for the UniFrame series platform
- Round and Square apertures
- Downlight, Adjustable accent and Wall wash configurations
- New 1" regress trim options
- 2-step color consistency and 90 CRI as a standard

- Versatile installation options including; New construction Non-IC, AirSeal IC, and Remodeler
- Up to 1800 lumens delivered
- Adjustable accent provides 45° vertical aiming











C3R/C3S Calculite LED

Round and Square 3" aperture downlights







Round Adjustable accent



Square Downlight & Lensed wall wash

Square Adjustable accent

Features

Aperture: 3" round/square Efficacy: up to 100lm/w Lumens: 500-1800 Watts: 7-20W Volts: 120-277V, 347V (50/60Hz) CRI: 90 (min) CCT: 2700-4000K Dimming: 0-10V, ELV Lifetime: 56,000 hrs (L70) Warranty: 5 year The adjustable accent features MesoOptics optical film to enhance optical performance. These films assist in reducing spill and providing homogeneous white light with the added benefit of optimizing luminaire efficiency. **More light, better light, and lower energy!**

Round styles



Lensed wall wash, Downlight, Shallow downlight & Adjustable accent All shown with Comfort clear reflector and Polished flange

Square styles



Lensed wall wash, Downlight, Shallow downlight & Adjustable accent All shown with Comfort clear reflector and Polished flange

Finishes



Specular clear



Comfort clear



Champagne bronze

Comfort clear diffuse

ise

White



Visit Signify.com/warranties for more information on Signify's standard 5-year limited warranty.



Tool-free installation using modular **quick connect technology**

See C3R & C3S specification sheets for additional drawings and technical information.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

(s) ignify

© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners. Signify North America Corporatio 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008