

Day-Brite

CFI

by @signify

Industrial

FCY

Value high bay



Modern industrial design, energy-saving technology

Functional high bay lighting has a new look with Day-Brite / CFI FCY LED high bay luminaires.

You don't need to sacrifice smart looks for affordable, dependable lighting in your functional spaces anymore. This high bay delivers up to 29,000 lumens with efficacies up to 129 LPW. Bring your retail and institutional spaces to life with this cost-effective luminaire built to last with a corrosion-resistant finish.

Performance meets style – no more sacrifice, just great looks, dependability and energy-savings.

DesignLights Consortium qualified
Please see the DLC QPL list for exact catalog numbers (<http://www.designlights.org/QPL>)

FCY LED value high bay

Indoor Industrial Luminaire

Features

Construction

Die formed sheet metal housing and end plates.

Finish

Corrosion resistant gloss white paint after fabrication finish.

Performance

Field CCT selectable for 4000K or 5000K.

Lens

Frosted acrylic diffuser provides wide light distribution and superior glare control.

Installation

V-hooks and 48" chains supplied (set of 2).

Wiring

Access plate located on top of housing for easy wiring.

Lumen maintenance

Up to 70% (L70) at 50,000 hours.

Certifications

Components are RoHS compliant and cULus listed for use in damp locations for -20C to 45C ambient.




Ordering guide

example: FCY15L840-UNV-DIM

Series	Lumens ¹ (nom)	Color Temp. (K)	Voltage	Dimming
FCY		8CST –	–	DIM
FCY Value high bay	15L 15,000 lm 22L 22,000 lm 29L 29,000 lm	8CST 80 CRI, Color Select (4000/5000K)	UN3 Universal voltage (120-277V) 347 347V	DIM 0-10V dimming

1. Nominal delivered lumens at 25°C ambient.

Dimensions



Accessories (order separately)

FCY-PENHGR

Pendant hanger accessory (adds 2.5" to height)

FCY-SBK

Surface bracket kit (adds 2.5" to height)

FCY-WG

Wire guard for FCY15 and FCY22

FCY-WG29

Wire guard for FCY29

MD360

Field installable motion detector



FCY-PENHGR



MD360



FCY-SBK



FCY-WG



5 year limited warranty

Visit [Signify.com/warranties](https://www.signify.com/warranties) for more information on Signify's standard 5-year limited warranty on complete luminaire systems.



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.