



Ordering guide

Example: HFP120 P4 A N PM

Product Code	Post Diameter	Finish	Arm Accessory	Post Matching
HFP120	P4		N	PM
HFP120 Twin	P4 4" Post Mount	A Black B White G Verde H Bronze I Gray J Green	N None	PM Post Matching

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Specifications

Housing

6063-T6 Extruded aluminum.

Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

Warranty

Three-year limited warranty.

Height	Length	EPA
35" (89 cm)	53 1/2" (136 cm)	3.05 sq. ft.

Internal Slip Fitter Height

19" (48 cm)

Internal Slip Fitter Diameter

3 1/2" (9 cm)

