



Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

### Ordering Guide

Example: R3 G

<b>Product Code</b>	R3	Aluminum Pathlyte
<b>Finish</b>	G	Verde

### Spacing Chart

### Specifications

#### HOUSING:

Single-piece cast aluminum. Stem is extruded aluminum. Fasteners are 300 series stainless steel. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

#### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

#### OPTICAL ASSEMBLY:

Painted, tempered glass jar with clear glass top.

#### LAMPING:

100W maximum A19 lamp. Lamp is not included. Lower wattage lamps are acceptable.

#### ELECTRICAL ASSEMBLY:

Medium base phenolic socket with nickel-plated screw shell and center contact. Fixture is pre-wired with 18 AWG black, white, and ground wires.

#### WARRANTY:

Three-year limited warranty.

#### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

<b>Height :</b>	<b>Width:</b>	<b>Max. Weight:</b>
18" (457mm)	9 1/8" (232mm)	4.2 lb.

