


P400


Twist-Lock Photocontrols

Features

- High-impact polycarbonate housing with 3-hole twist-lock connection.
- Features heavy-duty bi-metal switch that produces 30-45 seconds time delay.
- Fail mode ON, contacts normally closed.



Dimensions



Catalogue No.	Volts	Max. Watts Incandescent	Max. Watts HID	
			HPF	NPF
P400A	120	1000	1000	400
P400B	208/240/277	1000	1000	400
P400W	347	1000	1000	400

Job Information

Type:

Job Name:

Cat. No.:

Lamp(s):

Notes: