

LIGHTOLIER

by  Signify

Track Lighting

SlimSurface LED

S4S/S5R/S6S/S7R/S10R
Round & Square apertures



An easy to install architecturally pleasing low profile downlight

Leverages the latest LED technology, and features similar performance to typical recessed downlights but in a surface mount design.

Benefits

Delivering high lumen output and great visual comfort, this $\frac{5}{8}$ " surface mount downlight is appealing to both specifiers and contractors. SlimSurface is characterized by a completely flat lens with a narrow flange, giving it an architecturally pleasing look. This downlighting solution also eliminates the need for an AirSeal recessed housing or fire rated boxes, reducing material and installation costs.

- A very thin and architecturally pleasing solution with an integral driver for existing J-boxes or new construction
- Fits any ceiling and solves problem of limited plenum space
- Easy to install on j-boxes
- Provides an affordable alternative to Air-Seal IC recessed housings or Fire-Rated boxes
- 277V option for commercial lighting applications
- Choice of design with square and round apertures
- Glare controlling lens for comfortable light distribution
- Wet location listing allows for use in showers and bathrooms (if local code requires)



S4S / S5R / S6S / S7R / S10R SlimSurface LED

Round & Square apertures



A low profile LED downlight intended for ceiling or wall mount applications. This 5/8" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

Features


- Efficacy:** 42-70lm/w
- Lumens:** 650, 1000 & 2200
- Watts:** 9.5-28 W
- CRI:** 80 & 90 (min)
- CCT:** 2700K to 4000K
- Volts:** 120V (50/60Hz)
- Dimming:** 0-10V, Triac and ELV (trailing edge)
- Lifetime:** 50,000 hrs (L70)
- Labels:** cULus wet and damp location listed, ENERGY STAR® certified
- Warranty:** 5 year

Fixture

example: S5R830K7AL

| Series | CRI | CCT | Lumens | Finish | Dimming |
|---|---------------|--|-----------|----------------|------------------------|
| S4S SlimSurface 4" Square S5R SlimSurface 5" Round | 8 80 9 90' | 27K 2700K 30L 3000K 35K 3500K 40K 4000K | 7 650lm | - Matte White | - ELV / Triac (120V) |
| | | | | WH Matte White | Z10U 0-10V (120V-277V) |
| | | | | BK Matte Black | - ELV / Triac (120V) |
| | | | | AL Aluminum | Z10U 0-10V (120V-277V) |
| S6S SlimSurface 6" Square S7R SlimSurface 7" Round | 8 80 9 90' | 27K 2700K 30L 3000K 35K 3500K 40K 4000K | 10 1000lm | - Matte White | - ELV / Triac (120V) |
| | | | | WH Matte White | Z10U 0-10V (120V-277V) |
| | | | | BK Matte Black | - ELV / Triac (120V) |
| | | | | AL Aluminum | Z10U 0-10V (120V-277V) |
| S10R SlimSurface 10" Round ² | 8 80 9 90' | 27K 2700K 30L 3000K 35K 3500K 40K 4000K | 22 2200lm | - Matte White | - ELV / Triac (120V) |
| | | | | WH Matte White | Z10U 0-10V (120V-277V) |
| | | | | BK Matte Black | - ELV / Triac (120V) |
| | | | | AL Aluminum | Z10U 0-10V (120V-277V) |

Dimensions



1. CrispWhite can only be ordered with 90/30 CRI/CCT (930) combination.
2. SlimSurface LED 10" round installs into 4-11/16" J-box (not wet loc. listed).



Visit Signify.com/warranties for more information on Signify's standard 5-year limited warranty.

See specification sheet S4S/S6S & S5R/S7R/S10R for additional drawings and technical information.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

