








Gardco features a range of square and round poles suitable for site and area lighting.



Family	SSS or L/SSS	SRS or L/SRS	GTS	TRS	SSA	RA	TRA
Description	Straight Square Steel	Straight Round Steel	Tapered Square Steel	Tapered Round Steel	Straight Square Aluminum	Straight Round Aluminum	Tapered Round Aluminum
Nominal Height (ft)	10, 12, 14, 15, 18, 20, 25, 30, 35, 40	10, 14, 16, 20, 25, 30	20, 25, 30, 35, 39	20, 25, 30, 35, 39	8, 10, 12, 15, 16, 18, 20	8, 10, 12, 15, 18, 20	8, 10, 12, 14, 16, 20, 25, 28, 30, 35, 39
Diameter (inches)	4, 5, 6	3, 4, 5	3.05 x 5.25, 3.25 x 6.00, 3.11 x 6.41, 2.96 x 6.81, 2.92 x 7.18, 2.87 x 7.13	3.1 x 5.9, 3.7 x 6.5, 2.4 x 5.9, 3.5 x 7.0, 2.4 x 6.6, 3.8 x 8.0, 2.4 x 7.3, 3.6 x 8.5, 2.4 x 7.8, 3.6 x 9.0	4, 4.5, 5, 6	4, 4.5, 5	3 x 4, 3 x 5, 4 x 6, 4 x 7, 4.5 x 8, 6 x 10
Wall Thickness/Gauge	.125", .188" 11 ga., 7 ga.	.125", .188" 11 ga., 7 ga.	.125", .188" 11 ga., 7 ga.	.125" 11 ga.	.125", .156", .188", .250"	.125", .156", .188"	.125", .156", .188", .250"
Base	Cast Base				Cast Base Steel Tenon Base Hinged Base	Cast Base Steel Tenon Base Hinged Base	Cast Base
Bolt Circle (inches)	8.5, 11, 12 (+/- 0.5)	8.5 (+/- 0.5)	10.75, 12, 12.5, 13, 13.5	9, 9.5, 10, 10.5, 11, 11.5, 12.5	7, 9, 10, 11, 12	6.5 - 10 (varies)	6.5 - 14.5 (varies)
EPA 80 MPH	4.7 - 30.6	2.8 - 19.1	8.6 - 18.0	10.7 - 24.2	2.2 - 42.5	1.2 - 20.2	5.8 - 16.9
EPA 90 MPH	2.0 - 23.9	1.9 - 15.0	5.4 - 13.8	8.5 - 19.3	N/A - 32.7	N/A - 15.7	4.0 - 12.9
EPA 100 MPH	N/A - 18.9	1.3 - 12.2	3.0 - 10.7	6.6 - 15.6	N/A - 25.8	N/A - 12.6	2.8 - 10.1
EPA 110 MPH	N/A - 14.5	-	N/A - 8.4	5.5 - 13.0	-	-	-
EPA 120 MPH	N/A - 12.0	-	N/A - 6.5	4.5 - 11.0	-	-	-
EPA 130 MPH	N/A - 9.9	-	N/A - 5.1	3.5 - 9.3	-	-	-
Options	Duplex Receptacle, Ground Fault Receptacle, Festoon Outlet, Vibration Dampener, Additional Hand Hole, Couplings (Internal Thread), Nipples (External Thread)						
Finish	Bronze, Black, White, Medium Grey, Dark Grey, Galvanized, Lumec GY3, SolarForm Dark Grey (RAL 7011), Finish over Galvanized, Optional (e.g. RAL code), Special (custom color chip)				Bronze, Black, White, Medium Grey, Dark Grey, Lumec GY3, SolarForm Dark Grey (RAL 7011), Bronze Anodized, Black Anodized, Medium Grey Anodized, Optional (e.g. RAL code), Special (custom color chip)		
Limited Warranty	Minimum 1 year				1 year & 5 years		
Link					<b>SSA-CB SSA-STB SSA-HB</b>   	<b>RA-CB RA-STB RA-HB</b> 