


HOUSE SIDE




VERIFY BOLD LINE IS 8" LONG

12.75 SQUARE

STREET SIDE

- Ø 14.00 B.C.
- Ø 12.00 B.C.
- Ø 11.00 B.C.



- NOTES:
1. SUGGESTED BOLT CIRCLE: 12" DIAMETER
 MAXIMUM BOLT CIRCLE: 14" DIAMETER
 MINIMUM BOLT CIRCLE: 11" DIAMETER
 2. HADCO STRONGLY RECOMMENDS USING LEVELING NUTS TO MOUNT THE POST BASE. IF FOUNDATION IS NOT LEVEL, INCREASE 'X' DIMENSION ACCORDINGLY WHEN USING LEVELING NUTS WITH WASHERS.

 X = 3-1/4" WITH LEVELING NUTS
 X = 2-3/4" WITHOUT LEVELING NUTS
 3. IF USING GROUTING TO CONCEAL GAP BETWEEN BASE AND FOUNDATION, ALLOW FOR WATER DRAINAGE.

HADCO by Ignify	<small>CONFIDENTIAL: This drawing is confidential and proprietary to Signify Holdings and may not be reproduced in whole or in part without the express written consent of Signify Holdings. © 2018 Signify Holdings. All rights reserved.</small>	<small>TITLE: TEMP_AR_P2500 SERIES POST (FULL SIZE)</small>
	<small>UNLESS OTHERWISE SPECIFIED: *ALL DIMENSIONS ARE IN INCHES. *ALL THREADS ARE UNC-2B OR UNF-2B AFTER COATING. *ALL THREADS ARE TO BE VERIFIED WITH A THREAD GAUGE.</small>	<small>DRW SIZE: D</small> DRAWN BY: MATT PRESSEL DATE: 01/15/10 CHECKED BY: DATE: APPR BY: BILL DORON DATE: 01/15/10
<small>* DO NOT SCALE THIS DRAWING *</small>	<small>EF-04-01-11 Rev.09</small>	<small>SCALE 1:1 SHEET 1 OF 1 PART NO: 101000863</small>